



Part Number : [1301370127](#)
Product Description : Super-Safeway Multiple
Outlet Box, Standard Depth, 2-Sided, F2 (1/2"), NEMA
5-15 Duplex Receptacles with Flip Lids
Series Number : 130137
Status : Active
Product Category : Power Distribution
Engineering Part Number : 3005-1



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	Power Distribution
Series	130137
Description	Super-Safeway Multiple Outlet Box, Standard Depth, 2-Sided, F2 (1/2"), NEMA 5-15 Duplex Receptacles with Flip Lids
Enclosure Rating	NEMA 4
NEMA Configuration	NEMA 5-15
Product Name	Super-Safeway
Type	Multiple Outlet Box
UPC	78678874153

Agency

UL	E46237
----	--------

Electrical

Current - Maximum per Contact	15.0A
GFCI	No
GFCI Reset	N/A
Ground Continuity Monitor	No
Open Neutral Relay	N/A
Voltage - Maximum	125V

Physical

Cord Diameter	7.92-15.88mm (.312-.625")
Cord Grip Body Size	F2 1/2"
Cord Length	N/A
Cord Type	N/A
Feed-Thru	No
Flip Lid	Yes

Material - Housing	Rubber
Mounting Style	Portable
Net Weight	716.675/g
Number of Receptacles	2
Packaging Type	Carton
Receptacle Type	Duplex

This document was generated on Jun 03, 2026