

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories
→ Jumper Bars

General Information

Extended Product Type:	BJM6-2
Product ID:	1SNA168516R2500
EAN:	3472591685169
Catalog Description:	BJM6-2 POLES Jumper Bars
Long Description:	BJM6 - Jumper Bars - 2 poles - - 6mm Spacing.

Ordering

Color:	Grey
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85369010

Popular Downloads

Data Sheet, Technical Information:	1SNC160001C0207-CH-J Accessories
Instructions and Manuals:	1SNC160001C0207-CH-J Accessories

Dimensions

Product Net Width:	6 mm
Product Net Height:	21.5 mm
Product Net Depth / Length:	6 mm
Product Net Weight:	4 g

Technical

Function:	Jumper Bars
Rated Current (I_n):	Main Circuit 32 A
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Suitable For:	M2.5/6.4G.1 M4/6.3G

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C
---------------------------------	---------------------------

Certificates and Declarations (Document Number)

Instructions and Manuals:	1SNC160001C0207-CH-J Accessories
RoHS Information:	1SND230492F0201

Classifications

Object Classification Code:	X
ETIM 4:	EC000489 - Cross-connector for terminal block
ETIM 5:	EC000489 - Cross-connector for terminal block
ETIM 6:	EC000489 - Cross-connector for terminal block

Container Information

Package Level 1 Units:	10 piece
Package Level 1 Gross Weight:	0.04 kg
Package Level 1 EAN:	3472591685169
Package Level 2 Units:	1500 piece
Package Level 3 Units:	252000 piece

