



Technical Data

11.09.2023

Heat shrinkable tubing 6:1, adhesive lined in 1.2 m cuts
HA67 - thick wall adhesive lined

HA67-50.8/8.3

Article Number 321-30300



Material: Polyolefin, cross-linked (PO-X)
Colour: Black (BK)
Adhesive: Hot melt adhesive

Supplied Ø D min.: 50.8 mm
Recov. Ø d max.: 8.3 mm
Wall (WT): 4.8 mm
Shrink Ratio: 6:1
Longitudinal Change After Shrinkage: -10% max.
Min. Shrink Temperature - °C: +120 °C

Operating Temperature : -55 °C to +110 °C

Test Method

Dielectric Strength: 20 kV/mm
Tensile Strength: 14 MPa
Elongation at break: ≥400%

IEC 243



We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved