

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/15/043	

65

54

43



32

21

10

APPROVED: _____

DATE: _____ TITLE: _____



POSITIONS	Socket Dimensions			
	A	B	C	D
15	.643 (16.33)	.984 (24.99)	1.213 (30.81)	.759 (19.28)
26	.971 (24.66)	1.312 (33.32)	1.541 (39.14)	1.083 (27.51)
44	1.511 (38.38)	1.852 (47.04)	2.008 (50.94)	1.626 (41.30)
62	2.159 (54.84)	2.500 (63.50)	2.729 (69.32)	2.272 (57.71)

SPECIFICATIONS:

Material: Insulator: PBT, glass reinforced, rated UL 94V-0

Insulator color: Black

Contacts: Phosphor Bronze

Plating: Gold Flash over Nickel underplate overall

Electrical: Operating voltage: 250 VAC max

Current rating: 5 Amps max

Insulation resistance: 5000 Mohms min @ 500 VDC

Dielectric withstanding voltage: 1000 VAC for 1 minute

Temperature Rating: Operating temperature: -65°C to +125°C

Unit: Inch / mm

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES .X ± .10 ØX ± .10 .XX ± .020 ØXX ± .015 .XXX ± .015 ØXXX ± .010		ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710 D-SUB,HIGH DENSITY, STRAIGHT FEMALE SOLDER CUP	
DRAWN	SS	11/15/04	SIZE
CHECKED			PART NO.
APPROVED			HDTXX-SD-JS
			SCALE: NTS
			SHEET 1 OF 1