






APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	9/27/10	
A		UPDATE DRAWING	10/16/20	AY/OC



SPECIFICATIONS:

Material:

Insulator: Polycarbonate, rated UL 94V-0

Insulator color: Clear

Contacts: Copper Alloy

Plating:

Gold over Nickel underplate on contact area

(See chart for thickness)

Electrical:

Voltage rating: 150 VAC RMS

Current rating: 1.5 Amp

Contact resistance: 20 mohms max

Insulation resistance: 1,000 Mohms min @ 500 VDC

Dielectric withstanding voltage:

Contact to Contact: 1,000 VDC or AC Peak for 1 minute

Contact to Shield: 1,500 VDC or AC Peak for 1 minute

Mechanical:

Wire range: 24~26AWG Stranded wire, ϕ 0.89~0.99mm

Temperature Rating:

Operating temperature: -25°C to +55°C

Environmental:

Lead free, RoHS compliant



"X"	GOLD PLATING
U	15 μ m
W	30 μ m
G	50 μ m

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES

.X	$\pm .10$	ϕ .X	$\pm .10$
.XX	$\pm .020$	ϕ .XX	$\pm .015$
.XXX	$\pm .015$	ϕ .XXX	$\pm .010$

APPROVALS		DATE
DRAWN	AY	9/27/10
CHECKED	VW	9/27/10
APPROVED		

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE

MODULAR TELEPHONE PLUG, 8P8C, ROUND HOLE

SIZE X	PART NO. MTPR-88-X	REV. A
-----------	-----------------------	-----------

REF: S00005C	SCALE: NTS	SHEET 1 OF 1
--------------	------------	--------------