



Part Number : [1300940524](#)
Product Description : Support Grips for Fiber Optics, Closed Mesh, Single Eye, Bale Length 4", Cable Diameter 7.62-9.91mm (.300-.390"), Approximate Break Strength 136.08kg (300 lbs)
Series Number : 130094
Status : Active
Product Category : Cable Grips
Engineering Number : 36672



Documents & Resources

Drawings
[1300940524_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not saleable
China RoHS	Not saleable
EU ELV	Not saleable
Low-Halogen Status	Not saleable
REACH SVHC	Not saleable
EU RoHS	Not saleable

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Cable Grips
Series	130094
Description	Support Grips for Fiber Optics, Closed Mesh, Single Eye, Bale Length 4", Cable Diameter 7.62-9.91mm (.300-.390"), Approximate Break Strength 136.08kg (300 lbs)
Product Name	Fiber Optic
Type	Support Grip
UPC	78678836672

Agency

CSA	LR32159
-----	---------

Physical

Approximate Break Strength	136.08kg (300 lbs)
Bale Length	0.102m (4.00")
Body Style	Straight
Cable Diameter	7.62-9.91mm (.300-.390")
Color - Grommet	N/A
Eye Type	Single
Gender	N/A
Material - Body	N/A
Material - Grip	Non-magnetic Tin Bronze Wire
Mesh Length	0.064m (2.50")
Net Weight	1.000/g
Number of Holes	N/A
O-Ring	N/A

Thread Size	N/A
-------------	-----

This document was generated on Sep 17, 2025