Specifications





Photo is representative



Eaton PTS181233V075

Eaton Bussmann series PTS1812 PTC resettable fuse, 0.75 A hold current, 33 Vdc

General specifications

PRODUCT NAME	Eaton Bussmann series PTS1812 PTC resettable fuse
CATALOG NUMBER	PTS181233V075
UPC	051712351799
PRODUCT LENGTH/DEPTH	4.55 mm
PRODUCT HEIGHT	0.8 mm
PRODUCT WIDTH	3.25 mm
PRODUCT WEIGHT	0.05 g
COMPLIANCES	RoHS Compliant TUV
CERTIFICATIONS	cURus
PRODUCT TYPE	PTC resettable fuse

Powering Business Worldwide

Downloaded from Arrow.com.

Product specifications

USED WITH	Medical equipment, Telecommunications, computers and peripherals Medical equipment, telecommunications, computers and peripherals
AMPERAGE RATING	0.75 A hold current
FUSE INDICATOR	Non-indicating
MOUNTING METHOD	Resettable surface
PACKAGING TYPE	Standard
QUANTITY	1000
VOLTAGE RATING	33 Vdc
TYPE	Electronic
SPECIAL FEATURES	Halogen free, lead free
APPLICATION	Electronic circuits

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - PTS181233V075 Eaton PTS1812 6 60 volt dc surface mount resettable ptc data sheet

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

Downloaded from Arrow.com.