

Pushbutton, 16.2 mm, momentary contact function, 1 NO, bezel red



Description

Pushbutton with mounting hole diameter 16.2 mm, screw terminal, non-illuminated



technical data

> general

| | |
|--|---------------------------------------|
| Bezel color | red |
| Property of bezel / mushroom | opaque |
| Collar shape | round |
| Operating temperature, min. | -25 °C |
| Operating temperature, max. | 85 °C |
| Storage temperature, min. | -40 °C |
| Storage temperature, max. | 90 °C |
| illuminated | No |
| Packaging | Box |
| Packaging unit | 100 pcs. |
| net weight | 11 g |
| Operating life | 150,000 cycles |
| B10 | 195,000 cycles |
| Degree of protection, front side, according to DIN EN 60529 | IP40 IP65 IP65 with sealing cap |
| Minimum order quantity (MOQ) | 100 pcs. |
| RoHS compliant | Yes |
| REACH compliant | Yes |
| country of origin | HU |

direct links

> RAFI eCatalog

> mounting diameters

| | |
|---------------------------|---------|
| Outside dimension, length | 20 mm |
| Outside dimension, width | 20 mm |
| Outside dimension, height | 50 mm |
| Mounting hole | 16.2 mm |
| Mounting depth | 41 mm |
| Installation height | 9 mm |

> mechanical data

| | |
|------------------------|----------------------------|
| Actuation function | momentary contact function |
| Operating force, min. | 7,5 N |
| Operating travel, max. | 4.3 mm |
| Contact function | 1 NO |

| | |
|--------------------------|----------------|
| Contact system | Bridge contact |
| Contact material | Silver |
| Fixing | Threaded ring |
| Terminal on the rear | Screw terminal |
| > electrical data | |
| Rated voltage, max. | 250 V |
| Rated current, max. | 2 A |

drawings

Dimensioned drawing

