



LXDC2HL15G-303

DC/DC 5.5V Input, 1.0-2.5V Output, 2.5mm X 2.0mm
1.0mm(Height)

Recommended

In Production

?

[DATASHEET \(PDF\)](#)

[ADD TO COMPARE LIST](#)

[CONTACT US](#)

[SAMPLE REQUEST](#)

[TECHNICAL SUPPORT](#)

[REQUEST A QUOTE](#)

[STOCKCHECK: WHERE TO BUY](#)

[ROHS-CERTIFICATE](#)

Technical Information

Input Voltage Range (V)	2.3 to 5.5
Dimensions (mm)	2.5x2.0x1.0
Efficiency (%)	85
Output Current (A)	0.2
Operating Temp. Range (C)	-40 to 85
RoHS 6	Yes
Series Headline	Micro DC-DC Converters/Buck Type
Series Description	Micro DC-DC Converters/Buck Type
Total Output Power (W)	0.3
Output Voltage 1 (V)	1.5

