

3M Touch Systems

Products

[Multi - Touch Displays](#)
[Touchscreen Systems](#)
[Touchscreen Displays](#)
[Touchscreen Controllers](#)
[Touchscreen Software](#)
[Touch Screen Selector](#)

Applications

[Gaming](#)
[Retail](#)
[Financial](#)
[Transportation](#)
[Entertainment](#)
[Industrial](#)
[Healthcare](#)

Touchscreen Technologies

[Technologies](#)
[Touch Electronics](#)
[Materials](#)
[Manufacturing](#)

Information

[About 3M Touch Systems](#)
[Events](#)
[Technology and Application Briefs](#)
[Product and Technical Documents](#)
[Warranty Statement](#)
[Technology and Application Briefs2](#)

Support

[Download Touch Driver](#)
[Customer Service](#)
[Contact Us](#)

[Brasil](#) > [Produtos & Serviços](#) > [Elétricos, Eletrônicos e Telecomunicações](#) > [3M Touch Systems](#) > [Product Catalog](#)
[3M Touch Systems Catalog](#) > [Touch Systems](#) > [3M™ MicroTouch™ DST Touch System](#)

3M™ MicroTouch™ System DST2270DX, 47.10" USB/Serial Dual Mode Controller



[\[click to enlarge\]](#)

3M ID: DSTK9017 -3470 (98 -0003 -3386 -8)

[<< View other configurations of this product](#)

Viewing Area Dimension D = Diagonal W = Width H = Height	Outer Area Dimension D = Diagonal W = Width H = Height	Controllers Available UC = USB SC = Serial	Aspect Ratio	Cable Length inches (mm)	Cable Exit	Where to Buy
D: 47.10" (1196.3 mm) W: 41.20" (1046.36 mm) H: 23.29" (591.56 mm)	D: 48.43" (1230.2 mm) W: 42.01" (1067.00 mm) H: 24.10" (612.20 mm)	Included (98 -0003 -3388 -4)	Wide	12" (304.8 mm)	1:00	Select a Region 6
Aspect Ratio : Wide Controller : USB/Serial Dual -Mode Etch : N/A Precision Area Diagonal inches (mm) : Precision Area Width inches (mm) : Cable Termination : N/A Controllers Available : Included (98 -0003 -3388 -4) Glass Thickness inches (mm) : .09 (2.2) Precision Area Height inches (mm) : Touch Technology : 3M Dispersive Signal Technology						