



+ CABLE ASSEMBLIES

PLUGGABLE I/O CABLE ASSEMBLIES



✓ Active

TE CONNECTIVITY (TE)
CA MINI IO TYPE I PIGTAIL

2-2205129-5
TE Internal Number: 2-2205129-5

- EU RoHS Compliant
- EU ELV Compliant
- Cable Assembly Type Mini I/O
- Equalized No
- Wire Size (AWG) 26
- Wire Size (mm²) .129
- Overall Outside Cable Diameter .244 in, 6.2 mm

↓ PRODUCT DRAWING
English

DOCUMENTATION

Product Drawings
CA MINI IO TYPE I PIGTAIL
PDF
English

FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.
Please Note: Use the Product Drawing for all design activity.

Product Type Features

Cable Assembly Type Mini I/O
Shielded Yes
Connector Type (End A) RJ45 Plug
Cable Assembly Category Industry Standard
Product Designation Patch Cord
Performance Category Category 5E Performance for 10/100/1000BASE-T
Latching Style Slide Latch
Product Type Cable Assembly
Twisted Pairs Yes

Configuration Features

Number of Positions 8
Number of Signal Positions 8
Configuration Single-Ended

Electrical Characteristics

Impedance (Ω) 100

Signal Characteristics

Data Rate (Gb/s) 1

Body Features

Equalized No
Color Black
Jacket Material PUR
Shield Material Copper Alloy

Contact Features

Contact Mating Area Plating Material Gold
Contact Mating Area Plating Thickness .5 μm, 19.68 μin

Mechanical Attachment

Jack screw Without

Housing Features

Housing Material Thermoplastic

Dimensions

Wire Size (AWG) 26
Wire Size (mm²) .129
Overall Outside Cable Diameter .244 in, 6.2 mm
Cable Assembly Length 5 m [16.4 ft]

Operation/Application

Halogen Free Yes

Industry Standards

Flammability Rating UL 444
IEEE 1394 No

Other
CLOUDSPLITTER No

Statement of Compliance

Statement of Compliance
PDF