



Fiber Optic Patch Cord, LC to LC, OM3, twin zip, 3 m, aqua

OBSOLETE

Replaced By:

2105027	Fiber Optic Patch Cord, OM3, LC/LC duplex, 1.8 mm LSZH & OFNR, Aqua
FFXLCLC42	OM4 LC to LC, Fiber Patch Cord, 1.6 mm Duplex, Low Smoke Zero Halogen (LSZH)

Product Classification

Regional Availability	Asia Australia/New Zealand China EMEA Europe India
Portfolio	NETCONNECT®
Product Type	Fiber patch cord, duplex

General Specifications

Color, boot A	Beige
Color, boot B	Beige
Color, connector A	Beige
Color, connector B	Beige
Connector A, quantity	2
Connector B, quantity	2
Interface, Connector A	LC/UPC
Interface, Connector B	LC/UPC
Jacket Color	Aqua
Polarity	Pairs, flipped
Total Fibers, quantity	2

Dimensions

6536969-3

Cord Length	3 m 9.843 ft
Diameter Over Jacket	1.8 mm 0.071 in

Optical Specifications

Fiber Mode	Multimode
Fiber Type	OM3
Insertion Loss, maximum, connector A	0.3 dB
Insertion Loss, maximum, connector B	0.3 dB
Return Loss, minimum, connector A	30 dB
Return Loss, minimum, connector B	30 dB

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
---------------------	-------------------------------

Packaging and Weights

Packaging quantity	1
--------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted

