

Snap-in markers - UC-EM (20X7) - 0825499

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Snap-in markers, Sheet, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped into marker carrier, lettering field size: 20 x 7 mm, Number of individual labels: 20

Your advantages

- ✓ The markers, which are supplied in uniform sheets, can be labeled quickly and easily using the BLUEMARK LED
- ✓ The UC-EM ... UniCard labeling range includes markers for devices and switching devices from a wide range of manufacturers
- ✓ The format automatically ensures printing with a high degree of positioning accuracy
- ✓ The wide temperature range means that the labels can be used in control cabinets as well as the field
- ✓ The sheets provide space for including function texts

RoHS

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 046356 364317
GTIN	4046356364317
Weight per Piece (excluding packing)	10.000 g
Custom tariff number	39269097
Country of origin	Poland

Technical data

Dimensions

Length (b)	7 mm
Width (a)	20 mm

Ambient conditions

Snap-in markers - UC-EM (20X7) - 0825499

Technical data

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
---------------------------------	-------------------

General

Color	white
Components	free from silicone and halogen
Material	PA
Flammability rating according to UL 94	V2
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	20
Number of individual labels per row	5
Marking mounting type	snapped into marker carrier
Testing substances harmful to the wetting properties of lacquers (LABS conformity)	VW PV 3.10.7:2005-02
Result	Test passed
UV resistance	Following ISO 4892-2:2013-03
Result	Test passed
Test duration	96 h
Test for wipe resistance of inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Testing in a condensation changing climate in the presence of sulfur dioxide	following DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1,0 S
Cycles	2
Salt spray test	ISO 9227:2012-05
Result	Test passed

Environmental Product Compliance

China RoHS	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"
------------	---

Drawings

Pictogram



Snap-in markers - UC-EM (20X7) - 0825499

Classifications

eCl@ss

eCl@ss 10.0.1	27400629
eCl@ss 11.0	27281103
eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27149100
eCl@ss 5.1	27141100
eCl@ss 6.0	27149100
eCl@ss 7.0	27149129
eCl@ss 9.0	27400629

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 6.0	EC001288
ETIM 7.0	EC001288

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

Accessories

Accessories

Magazine

Magazine - P1 UC-MAG 6 - 5146121



Magazine, for CMS-P1-PLOTTER and PLOTMARK, for accommodating UC-EMP..., UC-EMLP...

Snap-in markers - UC-EM (20X7) - 0825499

Accessories

Printing system accessories

Ink cartridge - BLUEMARK CLED-FLUID-CARTR. - 5146662



Cartridge, for replacement, 20 ml UV color, black, including cleaning cartridge

Ink cartridge - BLUEMARK FLUID-CARTRIDGE - 5147421



Cartridge, for replacement, 28 ml UV color, black including cleaning cartridge

Ink cartridge - BM ID-CARTR. BK - 1044345



Replacement UV fluid, 23 ml, color: black

Ink cartridge - BM ID-CARTR. CY - 1044346



Replacement UV fluid, 23 ml, color: cyan

Ink cartridge - BM ID-CARTR. MA - 1044347



Replacement UV fluid, 23 ml, color: magenta

Snap-in markers - UC-EM (20X7) - 0825499

Accessories

Ink cartridge - BM ID-CARTR. YE - 1044348



Replacement UV fluid, 23 ml, color: yellow

Phoenix Contact 2021 © - all rights reserved
<http://www.phoenixcontact.com>