

## SKINDICHT® O-Ring NBR PG

SKINDICHT® O-Ring NBR PG, sealing ring, resistant to oil, dust and water, for a reliable sealing, ozone and UV-resistant, PG thread



UV-resistant

### Benefits

Resistant to oil, dust and water

### Application range

For a reliable sealing against foreign objects and liquids at the connecting thread of a gland or similar components.

### Note

Delivery will be made in the largest possible packing unit (bulk goods), minimum order quantity is one packing unit

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001181 ETIM 5.0 Class-Description: Sealing ring
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001181 ETIM 6.0 Class-Description: Sealing ring
Colour delivered:	Black
Material:	NBR
Temperature range:	-20°C to +100°C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products. Prices are net prices without VAT and surcharges. Sale to business customers only.

**SKINDICHT® O-Ring NBR PG**

Article number	Article designation / size	Inner Ø x thickness Ø (mm)	Pieces / PU
SKINDICHT® O-Ring NBR			
53001010	PG 7	10.0 x 1.5	100
53102011	PG 9	13.0 x 1.5	100
53001020	PG 11	16.0 x 1.5	100
52005740	PG 13,5	18.0 x 1.5	100
53001030	PG 16	20.0 x 1.5	100
52005750	PG 21	26.0 x 2.0	100
53001040	PG 29	34.0 x 2.0	50
52005760	PG 36	44.0 x 2.0	50
53001050	PG 42	50.0 x 2.0	50
52005770	PG 48	55.0 x 2.0	50

Last Update (05.09.2020)

@2020 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16