

Honeywell Pricebook - EMEA



**Solutions that
Enable Productivity**

Honeywell

Product Access Policy

Products on the pricelist are now classified in five categories: A, B, C, Virtual and New. These categories have been in place for legacy HSM products since 2013; the same categorization is now being introduced to legacy Intermec products. **Please note that for legacy Intermec products, the conditions and associated leadtime changes will not come into effect until April 2015; the classification indicated in the Pricelist is for information only at this time.**

For more easy understanding these categories carry in the Price List a corresponding color.

The categories reflect our high runners (A), medium runners (B) and low runners (C). These classifications will set clear expectations on the Lead Time and will increase our ability to meet the first promise dates.

The category Virtual is connected to our Service Contracts and Software products for which the aimed delivery is depending on the delivery of the hardware or is more a virtual transaction of the software key or contract. We are aiming to complete the virtual transaction within 3 working days.

The category New is referring to new products which will be assigned an ABC classification between 3-6 months after release, when the market trends have been reviewed and an ABC classification can be allocated per product item.

Media remains outside the scope of this categorization at this time.

The Pricelist with A, B, C, Virtual and New classifications is available on the Partner Web.

With the upcoming changes the aim is to deliver the following:

- Increased accuracy of our delivery dates.
- Better aligned Lead Times for core products and accessories considered as high and medium runners. Visibility on high/low runners, Visibility on made to order/ tailor made products (C category items), Visibility on non returnable & non cancellable (C category items).
- Quarterly review of classifications based on ordering pattern, market trends & product lifecycle.
- On a weekly basis a Lead Time map will be shared, providing you with updates on the exceptions in our supply chain including extended leadtimes and exceptional demand quantities.
- Please note: C items will be supplied within factory Lead Time and are non returnable.
- For all future orders a minimum order value is applicable. In case your sales order is not meeting the required minimum value, it still will be processed, but an administration fee will be added. You can find the minimum order value and corresponding fee on the pricelist on the partner web. Orders for demo units, Software, Service Contracts and OEM engines do not require a minimum value.
- Please ensure your purchase order specifies clearly when you have a requested delivery date that deviates from our published leadtimes.
- Amendments to orders will be accepted only within 24 hours after reception of the Order Acknowledgment.
- All cancellation requests are subject to approval and Honeywell reserves the right to charge additional fee with the minimum 10% of the ordered goods.

Scanning

Including cables and accessories

A	15 working days
B	15 working days
C	Factory Lead Time
New	Factory Lead Time
Virtual	not applicable (related to Software and Service Contracts)

Printing

Including cables and accessories

A	15 working days
B	20 working days
C	Factory Lead Time
New	Factory Lead Time
Virtual	not applicable (related to Software and Service Contracts)

Mobility, Supply Chain

Including cables and accessories

A	30 working days
B	30 working days
C	Factory Lead Time
New	Factory Lead Time
Virtual	not applicable (related to Software and Service Contracts)

RFID

Including cables and accessories

A	30 working days
B	30 working days
C	Factory Lead Time
New	Factory Lead Time
Virtual	not applicable (related to Software and Service Contracts)

Scanning - Vuquest® 3310g

Hardware - Kit

SKU	SKU Type	SKU Description	List (€)
3310g-4KBW-0	C	KBW Kit: 1D, PDF417, 2D gray scanner (3310g-4), 2.9m (9.5') straight KBW PS2 5V cable (52-52558-3-FR) and documentation	262.00
3310g-4USB-0	A	USB Kit: 1D, PDF417, 2D gray scanner (3310g-4), 2.9m (9.5') straight USB Type A, cable (52-52559-N-3-FR), documentation	257.00

Hardware - Scanner Only - cable sold separately

SKU	SKU Type	SKU Description	List (€)
3310g-4	A	Scanner: 1D, PDF417, 2D gray scanner (3310g-4) RS232/USB/KBW	247.00
3310g-4-1D	B	Scanner: 1D only, gray scanner (3310g-4) RS232/USB/KBW	213.00
3310g-4-EIO	C	Scanner: 1D, PDF417, 2D gray scanner (3310g-4) RS232/USB/KBW, External IO license	280.00
3310g-4-OCR	C	Scanner: 1D, PDF417, 2D, OCR, gray scanner (3310g-4) RS232/USB/KBW	280.00
3310GER-4	C	Scanner: 1D, PDF417, 2D, extended range focus, gray scanner, RS232/USB/KBW	247.00
3310GHD-4	C	Scanner: 1D, PDF417, 2D, HD focus, gray scanner, RS232/USB/KBW	247.00

Accessories - Cables

SKU	SKU Type	SKU Description	List (€)
52-52557-3-FR	A	Cable: RS232, black, DB9, 5V, 2.9m (9.5') straight	10.00
52-52558-3-FR	C	Cable: KBW, black, 3.0m (9.8'), coiled, 5V external power with ferrite	15.00
52-52559-N-3-FR	A	Cable: USB, black, Type A, 5V, 2.9m (9.5') straight	10.00
52-52561-3-FR	C	Cable: USB, black, Type A, 5V, 2.9m (9.5') straight, External IO	15.00
52-52562-3-FR	C	Cable: RS232, black, DB9, 5V, 2.9m (9.5') straight, External IO	15.00

Accessories - Power

SKU	SKU Type	SKU Description	List (€)
46-00526	A	Power Supply: EU plug, 1.0A @ 5.2VDC, 90-255VAC @ 50-60Hz	23.00
46-00870	A	Power Supply: UK plug, 1.0A @ 5.2VDC, 90-255VAC @ 50-60Hz	23.00

Software - Software

SKU	SKU Type	SKU Description	List (€)
TF2-EZBCBP	Virtual	Software: EasyBCBP license key for Xenon, Vuquest	73.00
TF2-EZDL	Virtual	Software: EasyDL license key for Xenon, VuQuest, Genesis 7580g-2 and Captuvo supports older GA DL encryption	73.00
TF2-EZGS1	Virtual	Software: EasyGS1 license key for Xenon, Vuquest	73.00
TF2-EZMVC	Virtual	Software: EasyMVC license key for Xenon, Vuquest	73.00

Accessories - Stands/Holders

SKU	SKU Type	SKU Description	List (€)
46-01210	B	Vuquest presentation-tray stand	61.00

Software - Software

SKU	SKU Type	SKU Description	List (€)
SW-2D-33xx	Virtual	Software: 2D license key for Vuquest 3310	46.00
SW-OCR-33xx	Virtual	Software: OCR license key for Vuquest 3310	33.00

Software - Software Licenses ☐ Multi-Year Bundle - includes Maintenance & Support - new customers minimum order of 10 licenses

SKU	SKU Type	SKU Description	List (€)
REM-CLIENT-SCAN-3Y	Virtual	Remote MasterMind - 1D or 2D Scanner license with three year of software maintenance and support included	31.00
REM-CLIENT-SCAN-5Y	Virtual	Remote MasterMind - 1D or 2D Scanner license with five year of software maintenance and support included	36.00

Software - Software Licenses - No Maintenance & Support Included - Existing Customers Only

SKU	SKU Type	SKU Description	List (€)
REM-CLIENT-SCAN-NM	Virtual	Remote MasterMind - 1D or 2D Scanner License - NO MAINT & SUPPORT. (Existing ReM customers only - visit http://remotemastermind.honeywellaidc.com/onlinequote) to calculate maintenance due	11.00

Software - Software

SKU	SKU Type	SKU Description	List (€)
SW-EIO-33xx	C	Software: External Input Output (EIO) license key for Vuquest 3310	33.00

Global Services - Service Contracts (Price if service purchased within 30 days of product shipment. Price is per unit per year, except for packages noted as 3 year or 5 year - those are per unit for the term.)

SKU	SKU Type	SKU Description	List (€)
HSVC3310g-SMS3	Virtual	VuQuest 3310g, SMS 1-day turnaround, comprehensive coverage, 3-Year	29.00
HSVC3310g-SMS5	Virtual	VuQuest 3310g, SMS 1-day turnaround, comprehensive coverage, 5-Year	50.00

Software - Software Licenses includes 1yr Maintenance & Support - new customers minimum order of 10 licenses

SKU	SKU Type	SKU Description	List (€)
REM-CLIENT-SCAN	C	Remote MasterMind - 1D or 2D Scanner license with one year of software maintenance and support included	20.00
REM-SERVER	C	Remote MasterMind - Server License (mandatory for all new customers - no charge)	CFQ

Software - Software Maintenance & Support Extensions and Renewals

SKU	SKU Type	SKU Description	List (€)
REM-MNT-SCAN-1MO	C	Remote MasterMind - Bioptic Scanner Software Maint. & Support 'True-up' - one month ext. - use to Align existing and new device maint. expiry date to match (co-termination). Pls go to http://remotemastermind.honeywellaidc.com/onlinequote for assistance	1.00
REM-MNT-SCAN-1YR	C	Remote MasterMind - 1D or 2D Scanning Device Maintenance & Support Extension - one year term maintenance and support extension per managed scanner (must be ordered with matching new client license) to obtain this special pricing.	7.00

Note: Global Services contracts availability varies per region.
Services such as Service Made Simple (SMS) are available in the EU, USA & Canada.
For countries outside of the EU, USA & Canada, please contract a Honeywell representative to confirm availability.

Prices are recommended resell prices only. HSM Distributors and Partners are free to define their own prices.

Honeywell official pricelist is the one regularly updated and published on this site.

All prices are subject to change without notice and will be confirmed upon reception of orders.

Although we have combined the legacy price guides, if you are ordering directly from Honeywell you will still need to continue with the existing process of placing split orders to each of the corresponding order management teams through your normal route.
We will provide further updates as this situation changes.
Thank you for your understanding and patience.

For more information on our products:
www.honeywellaidc.com

Honeywell Scanning & Mobility
9680 Old Bailes Road
Fort Mill, SC 29707
800.582.4263
www.honeywell.com

