



YFTW2208W



Active

YFTW2208W

Elect Cu Twin Insul Wire Ferrules, Smooth Funnel Entry, 22 AWG, 0.60" L, Tin Plated, Orange, For use on Cu Cond

Image | Line Art | 3D Model | Video | Customer Drawing

Email Datasheet

Print Datasheet

SpecificationsDocuments

Dimensional	General	Conductor(s)	Physical	Approvals / Certifications	Other Features
Dimensional					
D2 (in)				0.19	
D - in				0.07	
D1 (in)				0.06	
L1 (in)				0.60	
Total Length				0.30	
General					
Number of Conductors				2	
Product Description				Elect Cu Twin Insul Wire Ferrules, Smooth Funnel Entry, 22 AWG, 0.60" L, Tin Plated, Orange, For use on Cu Cond	
Conductor(s)					
Copper Solid Size (Range)				22	
Copper Stranded (Range)				22 AWG	
Physical					
Type of Plating				Tin - Electro Plated	
Plated (Yes or No)				Y	
Product Material				Copper	
Approvals / Certifications					
UL Listed				N	
CSA Certified				N	
ROHS Compatible				Compliant	
UL Recognized				N	
CULUS				N	
Other Features					
UPC				7818104823777	