

Aptiv Connection Systems Catalog

Customer Service

Samples Request

Find by Feature

Browse by Category

Browse by Application

Comparison List (0)

Share

Search

Enter part number or keyword

Search Results (1)

Search Options

1 Result(s): [All] - 12048450

☐ Compare

12048450 - Metri-Pack 480 Series
Female Sealed Tin Plating Tang
Terminal, Cable Range 0.50 - 1.00
mm2

☐ Compare

Metri-Pack 480 Series Female Sealed Tin Plating Tang Terminal, Cable Range 0.50 - 1.00 mm2

Part # 12048450



[Question about this product?](#)

Attributes

Documents (2)

Related Products (1)

Part # :	12048450
Description :	Metri-Pack 480 Series Female Sealed Tin Plating Tang Terminal, Cable Range 0.50 - 1.00 mm2
Product Type :	Terminal
Status :	✓ Active
Blade size [mm] :	4.8
Terminal Family :	M/P
Series :	480
Gender :	Female
Sealable :	Sealed
Material :	CuSn3Zn9
Weight [g] :	1
Plating :	Tin
Minimum Cable Diameter [mm] :	2.11
Maximum Cable Diameter [mm] :	2.68
Minimum Cable Core Cross Section [mm2] :	0.50
Maximum Cable Core Cross Section [mm2] :	1.00
Temperature Range :	-40 to 125
Voltage Drop :	Less than 3.0
RoHs compliant :	Yes
ELV compliant :	Yes

Certain products listed on this website may be subject to restricted usage or distribution or may not be available. For additional information, please contact your local sales office.

