

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1800814250](#)
Status: **Active**
Overview: [Down Light Modules](#)
Description: Down Light Module 80mm, Wide Flood - 50°, Neutral (4100K), Standard Flux

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)
[Product Literature \(PDF\)](#)
[Installation Guide \(PDF\)](#)

Agency Certification	
UL	E328924
General	
Product Family	Solid State Lighting
Series	180081
Array Type	N/A
Beam Angle	24°, 32°, and 50°
Comments	Commercially Configurable to 700mA, 1050mA, and 1400mA
Installation Guide Order No	987650-4385
Overview	Down Light Modules
Product Literature Order No	987650-4381
Product Name	Down Light Module
Type	LED Puck Module
UPC	884982218994
Physical	
Base Type	Socket
Color Rendering Index (CRI)	80
Correlated Color Temp (CCT)	4100K
Lamp Type	Light Module
Net Weight	64.640/g
Packaging Type	Individual Carton
Electrical	
Lamp Wattage - Maximum	12.4W, 17.2W, 7.9W
Lumens	1020, 550, 800
Voltage (Fixture) - Maximum	11.4V, 11.9V, 12.3V
Material Info	
Reference - Drawing Numbers	
Sales Drawing	SD-180081-000



Series image - Reference only

EU ELV
Not Reviewed

EU RoHS Not Reviewed REACH SVHC Not Reviewed Halogen-Free Status Not Reviewed Need more information on product environmental compliance?	China RoHS
--	-------------------

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed

Search Parts in this Series
[180081](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION