



Part Number : [1301350207](#)

Product Description : Super-Safeway GFCI Multiple Outlet Box, Open Neutral Relay, (2) NEMA 5-15 Duplex with Flip Lids, 0.305m (1.0') Cord Length, 12/3 SOOW Cord, NEMA 5-15 Plug

Series Number : 130135

Status : Obsolete

Product Category : Power Distribution

Engineering Number : 32G15E123



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Part Details

General

Status	Obsolete
Category	Power Distribution
Series	130135
Description	Super-Safeway GFCI Multiple Outlet Box, Open Neutral Relay, (2) NEMA 5-15 Duplex with Flip Lids, 0.305m (1.0') Cord Length, 12/3 SOOW Cord, NEMA 5-15 Plug
Enclosure Rating	NEMA 4
NEMA Configuration	NEMA 5-15
Product Name	Super-Safeway
Type	GFCI Multiple Outlet Box
UPC	78678876136

Electrical

Current - Maximum per Contact	15.0A
GFCI	Yes
GFCI Reset	Manual
Ground Continuity Monitor	No
Open Neutral Relay	Yes
Voltage - Maximum	125V

Physical

Cord Diameter	15.24mm (.600")
Cord Grip Body Size	F3 3/4"
Cord Length	0.305m (1.0')
Cord Type	12/3 SOOW
Feed-Thru	No
Flip Lid	Yes
Material - Housing	Rubber
Mounting Style	Portable
Number of Receptacles	2

Packaging Type	Carton
Receptacle Type	Duplex

This document was generated on Sep 24, 2025

Obsolete