

Specifications



Photo is representative



Eaton HCP0805-R40-R

Eaton HCP0805 inductor, 0.4 μ H, 20 A Irms, 32 A ISAT, 3.3 m Ω resistance, SMT mounting, Iron Powder, 2-pins, 700 qty.

General specifications

PRODUCT NAME	Eaton HCP0805 inductor
CATALOG NUMBER	HCP0805-R40-R
UPC	051712544238
PRODUCT LENGTH/DEPTH	7.9 mm
PRODUCT HEIGHT	5 mm
PRODUCT WIDTH	7.6 mm
PRODUCT WEIGHT	1.145 g
COMPLIANCES	RoHS Compliant

Product specifications

TYPE	Inductor
MOUNTING	SMT
IRMS	20 A
ISAT	32 A
PACKAGE QUANTITY	700
MATERIAL	Iron powder
FREQUENCY RATING	Up to 2 MHz
CONTACT CONFIGURATION	Two-pin
TEMPERATURE RATING	-40 to 155 °C
RESISTANCE	3.3 mΩ
SERIES	HCP0805

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - HCP0805-R40-R](#)

[Eaton HCP 0805 high current power inductors data sheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

