

NEW



Lexar® ARMOR GOLD SDXC™ UHS-II Card

Up to 280MB/s read, up to 205MB/s write

1TB

512GB

256GB

128GB

64GB

+ Compare

Specifications



Material	Stainless steel
Capacity	64GB, 128GB, 256GB, 512GB, 1TB
Performance	64GB-128GB Up to 280MB/s read, up to 210MB/s write 256GB-1TB Up to 280MB/s read, up to 205MB/s write
Form Factor	UHS-II
Video Speed Class	V60
Operating Temperature	-25°C to 85°C (-13°F to 185°F)
Storage Temperature	-40°C to 85°C (-40°F to 185°F)
Dimensions (W x L x H)	32mm x 24mm x 2.1mm / 1.25" x 0.95" x 0.08"
Weight	7.65g / 0.016lbs
Warranty	Limited lifetime warranty ²

¹ Up to 280MB/s read transfer, write speeds lower. Speeds based on internal testing. Actual speed may vary depending on host device.

² Limited lifetime warranty is limited to 10 years from purchase in Germany and regions not recognizing lifetime warranty.

370N Pressure Resistance

IP68 Dust and Water Resistant

5-Meter Drop-Proof

Temperature-Proof: Operation -25*to 85°C, Storage -40°C to 85°C

Wear-out resistance: up to 10,000 times of plugging and unplugging

Lexar is not liable for any loss of data or images. Product appearance, performance, software offerings, and packaging may vary depending on ship date and available inventory. Actual usable memory capacity may vary. 1GB equals 1 billion bytes.

Product Numbers



Global	Capacity	#Part
	64GB	LSDAMGL064G-RNNNG
	128GB	LSDAMGL128G-RNNNG
	256GB	LSDAMGL256G-RNNNG
	512GB	LSDAMGL512G-RNNNG
	1TB	LSDAMGL001T-RNNNG