

MICRO SWITCH
a Honeywell Division

FED. MFG. CODE 91929

SWITCH-BASIC

CATALOG LISTING
V7-1A37D8-000-3

CW-B0088

CATALOG LISTING

V7-1A37D8-000-3

REPLACES

RELEASE NO. PR-19025

M

ISSUE
4

CHECK

30 JAN 12

CMH

CHECK

27 DEC 89

J A P



CHECK

89 DEC 89

T J A

RASTER

DRAWN




NOTE

1 - SWITCH WILL OPERATE AND RELEASE WITHIN FULL EXCURSION OF THE PLUNGER

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE — — — 150 GRAM MAX
RELEASE TRAVEL — — — — .010 MIN
RELEASE FORCE — — — 25 GRAM MIN

DIFFERENTIAL TRAVEL — — .002-.010
OVERTRAVEL — — — — .050 MIN
FREE POSITION — — — — .625 MAX

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P N C

L162 5A 125, 250, 277 VAC
1/10HP 250 VAC



SCALE NONE DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE

ONE PLACE (.0) ±.030

TWO PLACE (.00) ±.015

THREE PLACE (.000) ±.005

ANGLES ±

WEIGHT