

VB RJ45 LaR -VB RJ45 LaR FRNC blue 7.5m




Image is for illustration purposes only. Please refer to product description.

Part number	09 48 858 5589 075
Specification	VB RJ45 LaR -VB RJ45 LaR FRNC blue 7.5m
HARTING eCatalogue	https://b2b.harting.com/09488585589075

Identification

Category	System cabling
Series	RJ45
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	HARTING VarioBoot RJ45 Preferred directions left/right
Connector 2	HARTING VarioBoot RJ45 Preferred directions left/right
Type of cable	Copper cable (round)
Description of the cable	Wiring 1:1 Flame retardant Halogen-free

Version

Cable length	7.5 m
Number of cores	8
Core structure	4x 2x AWG 26/7

Technical characteristics

Transmission characteristics	Cat. 6 _A Class E _A up to 500 MHz
Data rate	10 Mbit/s 100 Mbit/s 1 Gbit/s 2.5 Gbit/s 5 Gbit/s 10 Gbit/s



Pushing Performance
Since 1945

Technical characteristics

Limiting temperature	-20 ... +60 °C unmoved 0 ... +60 °C moved
Degree of protection acc. to IEC 60529	IP20

Material properties

Material (cable)	FRNC (LSZH)
Colour (cable)	Blue

Specifications and approvals

Specifications	ISO/IEC 11801
	IEC 61156-6
	IEC 60332-1 Flame retardancy
	IEC 60754-2 Halogen freeness
	IEC 60754-2 Non corrosive
	IEC 61034 Low smoke

Commercial data

Packaging size	1
Net weight	320 g
Country of origin	Latvia
European customs tariff number	85444290
GTIN	5713140250734
eCl@ss	27060308 Patch cord copper (data cable)