Part Number : 797580014
Product Description : Pre-Crimped Lead PicoBlade Female-to-PicoBlade Female, Tin (Sn) Plating, 300.00mm Length, 26 AWG, Black
Series Number : 79758
Status : Obsolete
Product Category : Power and Signal Cable Assemblies



Documents and Resources

Drawings

797580014_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Obsolete

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Power and Signal Cable Assemblies
Series	79758
Description	Pre-Crimped Lead PicoBlade Female-to-PicoBlade Female, Tin (Sn) Plating, 300.00mm Length, 26 AWG, Black
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	PicoBlade Crimp Terminals
Keyword	Pre-Crimped Leads
Product Name	PicoBlade
UPC	884982052789

Physical

Cable Length	300.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Black
Gender	Female-Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.670/g
Packaging Type	Bag
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 1061
Wire Size (AWG)	26

Mates With / Use With

Obsolete

Downloaded from Arrow.com.

Use with Part(s)

Description	Part Number
PicoBlade Single Row Receptacle Housings	51021

This document was generated on Sep 25, 2026

Obsolete

Downloaded from Arrow.com.