
Part Number : 539160808
Product Description : 0.50mm Pitch SlimStack Plug, Surface Mount, Dual Row, Vertical, 4.00mm Stack Height, without Solder Tabs, 80 Circuits, without Vacuum Pick-up Tape
Series Number : 53916
Status : Active
Product Category : Board-to-Board Connectors



Documents and Resources

Drawings

539160808_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Specifications

539169200-SPK-200.pdf

529910000-PS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Downloaded from Arrow.com.

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Board-to-Board Connectors
Series	0.5, BB H3/4
Description	0.50mm Pitch SlimStack Plug, Surface Mount, Dual Row, Vertical, 4.00mm Stack Height, without Solder Tabs, 80 Circuits, without Vacuum Pick-up Tape
Application	Board-to-Board
Component Type	Plug
Product Name	SlimStack
UPC	800753919396

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	50V

Physical

Breakaway	No
Circuits (Loaded)	80
Circuits (maximum)	80
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No

Downloaded from Arrow.com.

Keying to Mating Part	No
Lock to Mating Part	No
Mated Height	4.00mm
Mated Width	5.40mm
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Net Weight	261.328/mg
Number of Rows	2
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Locator	No
PCB Retention	No
Pitch - Mating Interface	0.50mm
Plating min - Mating	0.254µm
Plating min - Termination	0.102µm
Polarized to PCB	No
Shrouded	Shrouded
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Surface Mount

Mates With / Use With

Mates with Part(s)

Description	Part Number
0.50mm Pitch Vertical SlimStack Receptacls	52991
0.50mm Pitch Vertical SlimStack Receptacles	54167

Downloaded from Arrow.com.