



Part Number : 1300980174
Product Description : MAX-LOC Strain Relief Cord-Sealing Grip,1-1/4" NPT, Straight Male Cable Diameter 19.05-22.23mm (.750-.875")
Series Number : 130098
Status : Active
Product Category : Cable Grips
Engineering Number : 5568



Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
--------	--------

Category	Cable Grips
Series	130098
Description	MAX-LOC Strain Relief Cord-Sealing Grip, 1-1/4" NPT, Straight Male Cable Diameter 19.05-22.23mm (.750-.875")
NEMA Rating	NEMA 3R
Product Family	Strain-Relief Cord Grips
Product Name	MAX-LOC
Type	Strain Relief Grip
UPC	78678872137

Agency

CSA	LR32159
UL	E76954

Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	Straight
Cable Diameter	19.05-22.23mm (.750-.875")
Color - Grommet	N/A
Eye Type	N/A
Gender	Male
Material - Body	Nylon
Material - Grip	N/A
Mesh Length	N/A
Number of Holes	1
O-Ring	No
Thread Size	1 1/4" NPT

Use with Part(s)

Description	Part Number
MAX-LOC Lock Nut 1-1/4" NPT	<u>1300990146</u>

This document was generated on Sep 25, 2024