



**Part Number :** [09508041](#)

**Product Description :** KK 3.96mm Crimp Terminal Housing, Friction Ramp, 4 Circuits, Natural

**Series Number :** 41695

**Status :** Active

**Product Category :** Connector Housings

**Engineering Part Number :** 41695-N-B04



---

## Documents and Resources

### Drawings

[009508041\\_sd.pdf](#)

[PK-41695-001-001.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)


### Specifications

[PS-08-50-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### [Compliance Statements](#)

- EU RoHS

- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Connector Housings
Series	41695
Description	KK 3.96mm Crimp Terminal Housing, Friction Ramp, 4 Circuits, Natural
Application	Wire-to-Board
Comments	Glow Wire Equivalent Part Number 416952002
Product Name	KK 396
UPC	800754227681

### Agency

CSA	LR19980
UL	E29179

### Physical

Circuits (maximum)	4
Color - Resin	Natural
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No

Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	1.386/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.96mm
Temperature Range - Operating	See Product Specification

### Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
KK 396 Vertical Breakaway Headers	<a href="#"><u>41661</u></a>
KK 396 Right-Angle Breakaway Headers	<a href="#"><u>41662</u></a>
KK 396 Vertical Square Pin Breakaway Headers	<a href="#"><u>41671</u></a>
KK 396 Right-Angle Friction Lock Breakaway Headers	<a href="#"><u>41672</u></a>
KK 396 Vertical Headers with Friction Lock	<a href="#"><u>41791</u></a>
KK 396 Right-Angle Headers with Friction Lock	<a href="#"><u>41792</u></a>

### Use with Part(s)

Description	Part Number
Pre-Crimped Lead KK Plus 396 Female-to-KK Plus 396 Female, Tin (Sn) Plating, 150.00mm Length, 18 AWG, Black	<a href="#"><u>797582145</u></a>
Pre-Crimped Lead KK Plus 396	<a href="#"><u>797582146</u></a>

Female-to-KK Plus 396 Female, Tin (Sn) Plating, 300.00mm Length, 18 AWG, Black	
KK 396 Female Crimp Terminals	<u>2478</u>
KK 396 Female Crimp Terminals	<u>2578</u>
Female Crimp Terminals for 3.96mm Pitch Housings	<u>45570</u>
KK Trifurcon Female Crimp Terminals	<u>6838</u>
KK Trifurcon Female Crimp Terminals	<u>7258</u>

---

This document was generated on May 20, 2026