

# Han HP Base Panel



Image is for illustration purposes only. Please refer to product description.

Part number	09 39 016 0310
Specification	Han HP Base Panel
HARTING eCatalogue	<a href="https://harting.com/09390160310">https://harting.com/09390160310</a>

## Identification

Category	Hoods / Housings
Series of hoods/housings	Han® HP
Type of hood/housing	Bulkhead mounted housing

## Version

Size	16 B
Locking type	Screw locking
Field of application	Hoods/housings for rough environments

## Technical characteristics

Tightening torque	1 Nm Fixing screws M4
Tightening torque (screw locking)	3 Nm
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP66
	IP68
	IP69 / IPX9K acc. to ISO 20653

## Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR
RoHS	compliant



**Pushing Performance**  
Since 1945

## Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3)
	R7 (HL 1-3)

## Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984
Approvals	CE

## Commercial data

Packaging size	1
Net weight	127 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140056688
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466