



Part Number : 1300980200
Product Description : MAX-LOC Multi-Hole Strain Relief, 1/2" NPT, Straight Male with O-Ring, Cable Diameter 7.37mm (.290")
Series Number : 130098
Status : Active
Product Category : Cable Grips
Engineering Number : 5594-006W



Documents & Resources

Drawings
[1300980200_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not saleable
China RoHS	Not saleable
EU ELV	Not saleable
Low-Halogen Status	Not saleable
REACH SVHC	Not saleable
EU RoHS	Not saleable

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	Cable Grips
Series	130098
Description	MAX-LOC Multi-Hole Strain Relief, 1/2" NPT, Straight Male with O-Ring, Cable Diameter 7.37mm (.290")
Comments	Indicates that one or more grommet hole is covered by a thin membrane which can easily be "Poked" open if required.
NEMA Rating	NEMA 6P
Product Name	MAX-LOC
Type	Strain Relief Grip
UPC	78678818946

Agency

CSA	LR32159
UL	E76954

Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	Straight
Cable Diameter	7.37mm (.290")
Color - Grommet	Yellow
Eye Type	N/A
Gender	Male
Material - Body	Nylon
Material - Grip	N/A
Mesh Length	N/A
Net Weight	1.000/g
Number of Holes	2

O-Ring	Yes
Thread Size	1/2" NPT

Use with Part(s)

Description	Part Number
MAX-LOC Lock Nut 1/2" NPT	<u>1300990143</u>

This document was generated on Apr 25, 2025
