

Flat gasket - CES-B16-WRG-BK - 0801726

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Flat gasket made of NBR, size B16



RoHS

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 046356 675253
GTIN	4046356675253
Weight per Piece (excluding packing)	1.000 g
Custom tariff number	40169300
Country of origin	Germany

Technical data

Dimensions

Length	120 mm
Width	57.5 mm
Height	2.5 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 80 °C (static)
---------------------------------	---------------------------

General

Type	B16
Material	NBR
Color	black

Flat gasket - CES-B16-WRG-BK - 0801726


Technical data

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Drawings

Dimensional drawing



Dimensional drawing

Classifications

eCl@ss

eCl@ss 10.0.1	23071590
eCl@ss 11.0	23071590
eCl@ss 4.0	27081000
eCl@ss 4.1	27081000
eCl@ss 5.0	27081000
eCl@ss 5.1	27081000
eCl@ss 6.0	23071500
eCl@ss 7.0	23071590
eCl@ss 9.0	23071590

ETIM

ETIM 3.0	EC002317
ETIM 4.0	EC002498
ETIM 6.0	EC001181
ETIM 7.0	EC002498

UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	39121708

Flat gasket - CES-B16-WRG-BK - 0801726

Classifications

UNSPSC

UNSPSC 11	39121708
UNSPSC 12.01	39121708
UNSPSC 13.2	39131608
UNSPSC 18.0	31401601
UNSPSC 19.0	31401601
UNSPSC 20.0	31401601
UNSPSC 21.0	31401601

Approvals

Approvals

Approvals

DNV GL

Ex Approvals

Approval details

DNV GL		https://approvalfinder.dnvgl.com/	TAE00003VJ
--------	---	---	------------
