

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0009911500

Status:

Obsolete

Overview:

kk

Description:

3.96mm (.156") Pitch KK® Crimp Terminal Housing, Friction Ramp, 15 Circuits

Documents:

Drawing (PDF)

General

Product Family	Crimp Housings
Series	3069
Application	Power
Overview	kk
Product Name	KK®

Physical

Circuits (maximum)	15
Color - Resin	Natural
Gender	Female
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.96mm (.156")
Temperature Range - Operating	0°C to +75°C

Solder Process Data

Lead-free Process Capability	Wave Capable (TH only)
------------------------------	------------------------

Material Info

Old Part Number	306915
-----------------	--------

Reference - Drawing Numbers

Product Specification	PS-10-07, PS-99020-0087
Sales Drawing	SD-3069-N***



image - Reference only

Series

EU RoHS

ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product
environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series
3069Series

Mates With
2220 , 3190 , 3192 , 3243, 3246, A4042,
41661 , 41662 , 41671 , 41672 , 41681 ,
41682 , 41701 , 41711 , 41721 , 41741 ,
41761 , 41771 , 41772 , 41791 , 41792 ,
42441 , 42461 , 42471 , 42491 , 42492

Use With
2478 Crimp Terminals for 18-24 AWG, 2578
Crimp Terminals for 22-26 AWG

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION