

Specification Sheet

Part Number: 251-30709



Can be cut to length with scissors, eliminating waste and keeping stock to a minimum.
Available in 9 sizes, for thicknesses from .016" to .512", insuring proper fit.

Grommet, Panel Thickness 0.319"-0.382", PTFE, Natural, 9.7ft/pkg

Article Number	251-30709
Type	G51TG
Color	Natural (NA)
Quantity Per	reel
Product Description	HellermannTyton's Flexiform grommet is a unique, continuous wire protection product which fits easily in all shapes and sizes of holes without the aid of tools or adhesives. Flexiform grommet can be used on any type of material including wood, steel, aluminum, plexiglass, and glass.
Short Description	Grommet, Panel Thickness 0.319"-0.382", PTFE, Natural, 9.7ft/pkg
Global Part Name	G51TG-PTFE-NA

Length L (Imperial)	9.7
Variant	Open
Width W (Imperial)	0.52
Width W (Metric)	13.2
Height H (Imperial)	0.268
Height H (Metric)	6.8
Panel Thickness Min (Imperial)	0.319
Panel Thickness Max (Imperial)	0.382
Panel Thickness Min (Metric)	8.10
Panel Thickness Max (Metric)	9.70
Material	Polytetrafluoroethylene (PTFE)
Material Shortcut	PTFE
US MIL SPEC	MS21266-7T
Flammability	UL 94 V-0

Halogen Free	No
Operating Temperature	-76°F to +500°F (-60°C to +260°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	9.7
Package Quantity (Metric)	3
Customs Number	3926909988

© 2021 HellermannTyton. All Rights Reserved.

[Contact Us](#)
[RoHS/WEEE Compliance](#)
[Disclaimer](#)
[Terms and Conditions](#)