Part Number : 1300910202
Product Description : Woodhead Standard Duty Cord Reel with Flying Leads, 12/3 SJTOW Cord, 10.67m (35.0') Cord Length, NEMA 5-20 Straight Blade Plug
Series Number : 130091
Status : Active
Product Category : Electrical Reels
Engineering Part Number : 998



Documents and Resources

Drawings

1300910202_sd.pdf

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Downloaded from Arrow.com.

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Electrical Reels
Series	130091
Description	Woodhead Standard Duty Cord Reel with Flying Leads, 12/3 SJTOW Cord, 10.67m (35.0') Cord Length, NEMA 5-20 Straight Blade Plug
Enclosure Rating	NEMA 1
NEMA Configuration	NEMA 5-20
Product Name	Super-Safeway
Type	Cord Reel
UPC	78172548607

Agency

CSA	LR29921

Electrical

Current - Maximum per Contact	20.0A
GFCI	No
Lamp Wattage - Maximum	N/A
On/Off Switch	N/A
Voltage - Maximum	120V

Physical

Bulb Included	N/A
Cable Length	0.61m (2.0')
Cable Movement	Ratchet Lock

Downloaded from Arrow.com.

Cord Length	10.67m (35.0')
Cord Type	12/3 SJTOW
Depth	0.30m (11.75")
Drum Lock	Ratchet
Duty	Standard
Guide Arm	2 - Position
Height	0.36m (14.25")
Lamp Type	N/A
Material - Coating	Powder Coating
Material - Housing	Steel/Polycarbonate
Mounting Style	Rigid
Net Weight	9525.432/g
Number of Conductors	3
Packaging Type	Carton
Primary Cord/Cable Entry	N/A
Retraction Weight	1.4kg (3.0 lb)
Width	196.85mm (7.750")
Wire Size (AWG)	12

Downloaded from Arrow.com.