






APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/16/18	



RECOMMENDED PCB LAYOUT



MATE PLUG

Model No.	ASJ-195-V-HT	ASJ-195-L-HT	ASJ-195-B-HT	ASJ-195-C-HT	ASJ-195-D-HT
Schematic code					

SPECIFICATIONS:

Material:
Housing: Hi-Temp Thermoplastic, reated UL94V-0, Color: Black
Contacts: Copper Alloy
Plating:
Silver over Copper underplate overall
Electrical:
Rating: 30VDC, 0.5A
Contact Resistance: 30 mohm max.
Insulation Resistane: 100 Mohm min. @ 500 VDC
Dielectric withstanding voltage: 500 VAC
Temperature Rating:
Operating temperature: -20°C to +70°C
Environmental:
Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MILLIMETERS TOLERANCES: EXCEPT AS NOTED		<div>ADAM TECH</div> INTERCONNECTS		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
MM	ANGLE				
.X ± 0.50	X ± 5°				
.XX ± 0.30	.X ± 3°				
.XXX ± 0.15	.XX ± 2°				
APPROVALS		DATE		TITLE 3.5MM STEREO PHONE JACK, RIGHT ANGLE	
DRAWN	HR	11/16/18			
CHECKED	AC1	11/16/18			
APPROVED					
		SIZE X	PART NO. ASJ-195-X-HT	REV. -	
		REF: S00002C	SCALE: NTS	SHEET 1 OF 1	