



Minimum cable ϕ : $\phi_{Fmin}=3,0$

Maximum cable ϕ :

- with rubber bushing : $\phi_{Fmax}=9,0$
- without rubber bushing : $\phi_{Fmax}=12,0$
- without reduction plate: $\phi_{Fmax}=15$

		All Dimensions in mm Original Size DIN A4		Scale 1: 1		Free size tol.		Ref.		
								Sub.		
		All rights reserved		Created by DOUGE		Inspected by BAGDIKIAN		Standardisation HOFFMANN		
		Department EC PD - FR				Date 2013-02-05		State Final Release		
HARTING Electronics GmbH D-32339 Espelkamp		Title D-Sub Hood 37P side entry full metal							Doc-Key / ECM-Nr. 100521763/UGD/001/A 500000056836	
		Type TB		Number 09670370335					Rev. A	Page 1/1

09670370335

M3

Part number

screw thread