



DIMENSIONS mm (inches)



PART NUMBER		8609		76		8	
PIN OUT		rows a-b-c		3		24	
rows a-c		4		16			
NUMBER OF CONTACTS							
TERMINATION		L = 2.70 ± 0.25 (.106)		24			
L = 4.65 ± 0.25 (.183)				14			
OPTIONS		no option		7			
with harpoons				H			
PERFORMANCE CLASS		DIN 41612 class 3		4			
DIN 41612 class 2				5			
DIN 41612 class 1				6			
TERMINATION TYPE		LEAD FREE		E1LF			

PCB DRILLING

component side



GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C-8609-0000A

rev	ecn no	dr	date
A	-	MJA	2012-08-09
B	ELX-I-40683	MJA	2020-04-19
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection mm	
			ANGULAR		TOLERANCES UNLESS OTHERWISE SPECIFIED		size A3	
Dr M JACOB 2012-06-27			LINEAR		0.X		Scale 1.5	
Eng M JACOB 2012-06-27			0.XX		±0.1		ECN ELX-I-40683	
Chr M JACOB 2021-04-19			0.XXX		±0.1		Spec ref -	
Appr SANOJ 2021-04-19			Product family		DIN 8609		Rev. B	
Amphenol FCI			title		STRAIGHT MALE - STYLE R/2		dwg no C-8609-2292	
			SOLDER TO BOARD				CUSTOMER sheet 1 of 1	
			catalog no		-			