

6

5

4

3

2

1

D

C

B

A

L = 1.0 m : 20 87 145 3002 100
L = 2.0 m : 20 87 145 3002 200

* If a different length is required, contact your local HARTING office for part numbers and support.

MATING FACE
(male)

PIN-OUT

MALE INSERT	CABLE	FEMALE INSERT
PIN 1	#1 (BLACK)	PIN 1
PIN 2	#2 (BLACK)	PIN 2
PIN 3	#3 (BLACK)	PIN 3
PIN 4	#4 (BLACK)	PIN 4
PIN 5	#5 (BLACK)	PIN 5
PIN 6	#6 (BLACK)	PIN 6
PIN 7	#7 (BLACK)	PIN 7
PIN 8	#8 (BLACK)	PIN 8
PE	GREEN/YELLOW	PE

MATING FACE
(female)

DESCRIPTION	REV	DATE	NAME
RELEASED FOR PRODUCTION	A	10/16/15	ERW
PRELIMINARY RELEASE	-	08/11/15	WOODWORTH

Standard HARTING tolerances apply unless otherwise specified.

This drawing is property of HARTING Manufacturing Inc. No exploitation or transfer of information contained herein is permitted without written consent / agreement of HMI.

HARTING INC. OF NORTH AMERICA
1370 BOWES ROAD
ELGIN, IL 60123 PH: (847) 741-1500

HARTING PART NUMBER
20 87 145 3002 L00

DESCRIPTION
**UL2237 Cable Assembly
Han Q 8/0, side-entry, 1-lever**

DRAWING NUMBER
20871453002L00

REFERENCE
UL2237 ASSEMBLIES

SHEET
1/1

REVISION
A

Notes:
1. Contacts use crimp style termination.

Downloaded from [Arrow.com](#)