

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
MINNEAPOLIS, MINN 55402

FED. MFR. CODE 91929

SWITCH - BASIC

CATALOG LISTING
BZ-7RW822-A2

AQK1000

BZ-7RW822-A2

PAGE 1 OF 1

DRAWING NUMBER

ISSUE 10

REPLACES

RELEASE NO.

CHECK

REVISIONS

A	CO-16736	6 CH	5 APRIL 82
B	CO-34308	D J W	15 JUL 79
C	CO-70184-6	G J W	16 MAR 92
D	CO-73287-J	J A L	22 NOV 93
E	CO-75204-B	W L S	1 FEB 94
F	CO-77589	T S M	29 MAR 94
G	CO-93346	DLT	20 SEP 98
H	0017585	LKM	20 FEB 06

CHECK

17 APR 62

DAW

CHECK


5 APRIL 62

DAW

GCH

FORMTEK

0-30378



NOTE
MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON 1.000±.002 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE ----- 7 OZ MAX
RELEASE FORCE ----- 1 1/2 OZ MIN
DIFFERENTIAL TRAVEL ----- .020-.050
OVERTRAVEL ----- .094 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

-L96- 15A-125, 250, OR 480 VAC
1/2 A-125 VDC; 1/4 A-250 VDC
1/8 HP-125 VAC; 1/4 HP-250 VAC

-L288-
-L315-
-L306-

CE SP 505 RU

16A 250V ~ T85 5E4

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES

TOLERANCES ARE:
ONE PLACE (.01) ±.005
TWO PLACE (.00) ±.015
THREE PLACE (.000) ±.005
ANGLES ±

WEIGHT .076 LB