



Part Number : [190080006](#)

Product Description : Flag Krimptite Quick Disconnect, Female, for 18-22 (0.80-0.35mm²) Wire, Box, Tab 6.35 x 0.81mm, Carton

Series Number : 19008

Status : Active

Product Category : Quick Disconnects

Engineering Part Number : AA-1158



Documents and Resources

Drawings

[190080006_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)


Specifications

[PS-19902-005-001.pdf](#)

[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

| | |
|--------------------|---|
| GADSL/IMDS | Compliant with Exemption 44 |
| China RoHS |  per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

[Compliance Statements](#)

- EU RoHS

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

| | |
|--------------|---|
| Status | Active |
| Category | Quick Disconnects |
| Series | 19008 |
| Description | Flag Krimptite Quick Disconnect, Female, for 18-22 (0.80-0.35mm ²) Wire, Box, Tab 6.35 x 0.81mm, Carton |
| Product Name | Krimptite |
| Type | Flag Terminal |
| UPC | 800755046526 |

Agency

| | |
|-----|---------|
| CSA | LR18689 |
| UL | E79133 |

Electrical

| | |
|-------------------|------------------------|
| Voltage - Maximum | Per Wire Specification |
|-------------------|------------------------|

Physical

| | |
|-------------------|--------|
| Barrel Type | Closed |
| Gender | Female |
| Glow-Wire Capable | No |

| | |
|--------------------------------|------------------------|
| Insulated | No |
| Insulation | None |
| Lock to Mating Part | No |
| Material - Metal | Brass |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Net Weight | 0.713/g |
| Orientation | Flag |
| Packaging Type | Carton |
| Plating min - Mating | 2.540µm |
| Plating min - Termination | 2.540µm |
| Polarized to Mating Part | No |
| Tab Thickness | 0.81mm |
| Tab Width | 6.35mm |
| Temperature Range - Operating | Per Wire Specification |
| Termination Interface Style | Crimp or Compression |
| Wire Size (AWG) | 18, 20, 22 |

Solder Process Data

| | |
|------------------------------|-----|
| Lead-Free Process Capability | N/A |
|------------------------------|-----|

Application Tooling

Global

| Description | Part Number |
|--|------------------|
| PremiumGrade Hand Crimp Tool for Flag Krimptite/Vibrakrimp Un-insulated Female Quick Disconnect Terminals, 22-14 AWG | <u>640034200</u> |

This document was generated on May 19, 2026