

Quick Links

Cross reference

RoHS/LF P/N Search

Industry Standards

Alphabetical List

Documentation

3D model search

Customer drawing search

Multi Selection Search

Search by category

Start > Search=10123196-200L001* > 10123196-200L001

10123196-200L001

10123196-200L001 - IOconnections : MiniSAS HD Active Optical Cable, LSZH, 1 meter, straight cable exit

MATURE

Distributor Stock

Print Datasheet

FCI Brings You More

Contact our sales/technical support

Sample request

Customer drawing

Product Environmental Compliance Report

Specifications

Download document

Mating Half

General Dimensional Electrical Mechanical Physical Approvals / Certifications Other Features	
General	
Cable Exit Style	straight
Fiber Type	OM2
Product Type	Active Optical Cable
Cable Colour	Orange
Dimensional	
Cable Length	1 meter
Electrical	
Power	0.8 Watts per end
Signal Speed	12 Gb/s per lane (4 lanes)
Power Supply Voltage	3.3V
Mechanical	
Durability (Mating cycles)	50 Cycles
Insertion force (Plug contact)	40 N
Retention force (Plug contact)	90 N
Physical	
Cable Type	Low Smoke Zero Halogen (LSZH)
Temperature (Range)	-5°C to +70°C
Approvals / Certifications	
Approvals / Certifications	UL, TUV and FDA Approved
UL File Number	E251142
TUV File Number	DE2-015589
FDA File Number	0312716-411
Other Features	
Packaging (Type)	high shield ESD bubbly wrap bag
Literature	mini-sas-hd-aoc-datasheet.pdf

Disclaimer : The information above is for reference only. For more technical details, refer to product specification and application specification.