

[Sign in](#)[Subscribe](#)[Change Country](#)[Consumer Products](#)[Industrial Solutions](#)[Support](#)[Compatibility](#)[About Transcend](#)[Home](#) » [Industrial Solutions](#)

## Industrial Solutions

### Services

#### Overview

#### Why choose Transcend

#### Quality

#### Business Partners

[Industrial Flash](#)[Industrial DRAM](#)[Applications](#)[Contact](#)[OEM Solutions](#)[\[ Industrial eCatalog \]](#)

### Industrial Temp microSDHC10I SDHC card



#### Download

- [Industrial eCatalog](#)
- [Certification](#)

[Compare](#)[Contact](#)[Intro](#) | [Features](#) | [Specifications](#) | [P/N](#)

### Specifications

Interface(connector)	microSD flash card connector
Form Factor	microSDHC flash card
Flash Type	MLC
Capacity(GB)	4GB/ 8GB
Max. R/W Performance(MB/s)(Vary by density)	Read: 18MB/s, Write: 15MB/s
Op. Voltage(V)	2.7V ~ 3.6V
Power Consumption(W)	0.72W
Op. Temp.(°C)	- 40°C ~ 85°C
Storage Temp.(°C)	- 40°C ~ 85°C
Humidity(%)	0% ~ 95%
Shock(G)	600G
Vibration(Hz/G)	20G (Peak-to-Peak), 20Hz to 2000Hz(Frequency)
Dimensions(mm)	11mm × 15mm × 1mm
MTBF(hours)	1,000,000 hours

### P/N

Capacity	P/N	Description
4G	TS4GUSDC10I	Industrial Temp microSD card
8G	TS8GUSDC10I	Industrial Temp microSD card

[Contact](#) | [Terms of Use](#) | [Privacy Policy](#) | [Careers](#) | [Where to Buy](#) | [Press Center](#) | [Site Map](#)

Copyright© 2013 Transcend Information, Inc. All Rights Reserved.