






插頭部件 (Plug Component)			頭部剥皮尺寸 (Dimensions)			線材規格 (Wire Styles)	尾部剥皮尺寸 (Dimensions)			端子規格 (Terminal Style)	
顏色(Color)	零件描述(Component)	Qty.	內剥(Strip)	外剥(ROJ)	顏色(Color)	SJT 18AWGx3C (Shielded, A+E) 105°C 黑色 (Black) Length : 3000±50 (118"±2")	外剥(ROJ)	內剥(Strip)	顏色(Color)	規格描述(Instruction)	端子編號(Style No.)
35P 黑色 (Black)	ME-302 (IEC 60320, C13)	1	6 ⁺¹ ₋₀	18±2	黑/Black(L)		50.8±5	6.35±3	黑/Black(L)	絕緣依尺寸剥除,留膠於線上 (Strip and Retain Outside Insulated)	
銅本色 (Brass-Natural)	2.0*4.0 方管端子(GEM 98752A-0) (2.0*4.0 Receptacle Terminal)	3	6 ⁺¹ ₋₀	18±2	白/White(N)		50.8±5	6.35±3	白/White(N)	絕緣依尺寸剥除,留膠於線上 (Strip and Retain Outside Insulated)	
米白色 (Off-White)	GA005-5 品字母插兩件式內模 (Computer 2x4 Serial Housing)	1	6 ⁺¹ ₋₀	18±2	綠/Green(E)		50.8±5	6.35±3	綠/Green(E)	絕緣依尺寸剥除,留膠於線上 (Strip and Retain Outside Insulated)	



			線材印字 (Wire Printed)		充麻, 油墨印字 (Fillers, Printing Ink)			CnC Tech, LLC					
F	REV	DATE	REVISE CONTENT	NOTE: 1 . Hi-Pot Test : 1500V/1Sec ; <0.5mA. 2 . Insulation Resistance Test : DC 500/min>100 meg-ohm. 3 . Continuity & Polarization Test : No short circuit, break circuit, displacement. 4 . Each end terminal shall be capable of withstanding a pull of 25lbs for 1 minutes without loosening. 5 . Strain relief shall be capable of withstanding a pull of 35lbs for 1 minutes without loosening. 6 . All material according to Non-toxic standard.(Material must be RoHS compliant.) 7 . "FMC" logo maybe present on C13.	包裝方式 (Packing)		DRAWN		Industrial Cable and Connector Technology				
	A	08/30-2012	The first edition is issued and drawing.		Tied Hank	See Hank Detail	Chu8.		CUSTOMER				
					Carton Size	480 x 320 x 230	DATE		P/N No.	800-1809-2-SJT0-BL-00300			
					Pack Number	100pcs/ UL Laster Labels	08/30-2012		MATERIAL	PVC	UNIT	mm	
					Carton Print	See Purchase Order			Customer Approval				
					TYPE	IEC 60320, C13 to ROJ(S&R)Power Supply Cord							
					DRAWNING NO.	098MM1003		REV	A				