Catalog



Swage Standoffs

Model: 3109-B-632-B

Select Finish

-0 No Plate

Select Finish

-0 No Plate

RFQ

Choose a CAD format | Download CAD

View 3D Model | View 2D Drawing | View Spec Sheet

Product Details

These standoffs are made of Brass. They are Round shaped with diameter as 3/8. The thread for this part is 6-32 and length is 1/4".

SWAGE TOOLING		
±.003	S	P
.075	A	1/32
.105	B	1/16
.135	C	3/32
.165	D	1/8
.230	E	3/16
.290	F	1/4

PDF Catalog

RAF_catalog_0099.pdf

Thread	6-32
O.D.	3/8"
Shape	Round
Length (L)	1/4"
Material	Brass
RoHS	Yes
Shank Length	0.105"
Board Thickness	1/16"
Shank Diameter	0.234"
Thread Clearance	0.200"
Finish	-0 No Plate

Downloaded from Arrow.com.