
Part Number : 2215973002
Product Description : PowerWize 3.40mm, 2-circuit, Mechanical Keying Option 2, Color Coded Natural, Receptacle Housing, Bag
Series Number : 221597
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

2215973002_sd.pdf

2215973001-PK-000.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

2215971000-AS-000.pdf

2215970001-PS-000.pdf

2215973000-TS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

Downloaded from Arrow.com.

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	221597
Description	PowerWize 3.40mm, 2-circuit, Mechanical Keying Option 2, Color Coded Natural, Receptacle Housing, Bag
Application	Wire-to-Board, Wire-to-Wire, Wire-to-Panel
Component Type	Receptacle
Product Name	PowerWize
UPC	196823670978

Agency

CSA	LR19980
UL	E29179

Physical

Circuits (maximum)	2
Color - Resin	Natural
Diameter	3.40mm

Downloaded from Arrow.com.

Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Polybutylene Terephthalate (PBT)
Net Weight	6.740/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	N/A
Pitch - Mating Interface	11.00mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +125°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
PowerWize 3.40mm, 2-circuit, Solder Tail, Mechanical Keying Option 2, Color Coded Natural, Right Angle Header, Tray	2218873322
PowerWize 3.40mm, 2-circuit, Solder Tail, Mechanical Keying Option 2, Color Coded Natural, Vertical Header, Tray	2218883322
PowerWize 3.40mm, 2-circuit, Mechanical Keying Option 2, Color Coded Natural, Plug Housing, Bag	2281860002
PowerWize 3.40mm, 2-circuit, Mechanical Keying Option 2, Color Coded Natural, Plug Housing with Panel Mount Ears, Bag	2281870002

Use with Part(s)

Description	Part Number

Downloaded from Arrow.com.

PowerWize 3.40mm Silver Plated Copper Alloy Crimp Sockets	221616

Application Tooling

Global

Description	Part Number
Tool for Extraction of PowerWize 3.4 Crimp Terminals from Receptacle Housing, 10-8 AWG	2002223300

Downloaded from Arrow.com.