Part Number : 395388012
Product Description : 5.08mm Pitch Eurostyle Vertical Dual Level PCB Header, Closed Ends, Green Housing, 12 Circuits
Series Number : 39538
Status : Active
Product Category : Terminal Blocks and Barrier Strip



Documents and Resources

Drawings

395388012_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

Downloaded from Arrow.com.

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Terminal Blocks and Barrier Strip
Series	39538
Description	5.08mm Pitch Eurostyle Vertical Dual Level PCB Header, Closed Ends, Green Housing, 12 Circuits
Application	Wire-to-Board
Component Type	PCB Header
Product Name	Eurostyle Pluggable
Type	PCB Terminal Blocks and Connectors
UPC	822350831567

Electrical

Current - Maximum per Contact	15.0A
Voltage - Maximum	300V

Physical

Circuits (Loaded)	12
Circuits (maximum)	12
Color - Resin	Green
Entry Angle	N/A
Lock to Mating Part	Yes
Number of Rows	2

Downloaded from Arrow.com.

Orientation	Vertical
Panel Mount	No
PCB Thickness - Recommended	3.00mm
PC Tail Length	3.50mm
Pitch - Mating Interface	5.08mm
Pitch - Termination Interface	5.08mm
Polarized to Mating Part	Yes
Shrouded	Closed Ends
Stackable	No
Temperature Range - Operating	-40° to +105°C
Wire Size (AWG)	N/A

Solder Process Data

Max-Duration	5
Lead-Free Process Capability	REFLOW
Max-Cycle	135
Max-Temp	260

Mates With / Use With

Mates with Part(s)

Description	Part Number
5.08mm Pitch Eurostyle Horizontal Plugs	39530
5.08mm Pitch Eurostyle Vertical Plugs	39533
Mates With	Most 5.08mm (.200") Pitch Industry Standard Plugs

Downloaded from Arrow.com.