



Part Number : [1300540043](#)
Product Description : Micro-Change (M12) D-Coded to RJ-45 Adapter, Straight to Straight, 4-Pole Female to RJ45 Male, 0.50m (1.64') Length
Series Number : 130054
Status : Active
Product Category : Circular Industrial Connectors
Engineering Number : ER1PAB3004M005



Documents & Resources

Drawings
[Drawing 1300540043_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3 per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	130054
Description	Micro-Change (M12) D-Coded to RJ-45 Adapter, Straight to Straight, 4-Pole Female to RJ45 Male, 0.50m (1.64') Length
IP Rating	IP67
Product Family	Brad Industrial Ethernet Solutions
Product Name	Micro-Change (M12),RJ45
Type	Double Ended
UPC	78172565541

Agency

UL	E361772
----	---------

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	125V

Physical

Coupling Type	External Thread
Gender	Female-Male
Keyway	D-Coded
Length	0.50m
Material - Component	Nickel-plated Brass
Mounting Thread Size	PG9
Net Weight	55.000/g
Orientation	Straight
Panel Mount	Back

Poles	4
Temperature Range - Operating	-25° to +75°C
Wire/Cable Type	Unshielded TPE/AWM 2463
Wire Size (AWG)	24

This document was generated on Sep 28, 2024