



TERMINALS & SPLICES

KNIFE DISCONNECTS



✓ Active

TE CONNECTIVITY (TE)

KNIFE DISCONNECT, PIDG 22-16

PIDG

32446

TE Internal Number: 32446

EU RoHS Compliant

EU ELV Compliant

Plating Material Copper, Tin

Packaging Method Box

Wire Size (AWG) 22 – 16

Wire Size (mm²) .3 – 1.42

Insulated Yes

PRODUCT DRAWING
 English

3D PDF


DOCUMENTATION

Product Drawings

TERMINAL, KNIFE DISCONNECT, P.I.D.G., WIRE SIZE,22-16 AWG

PDF

English

CAD Files

Customer View Model

2D_DXF.ZIP

English

3D PDF

PDF

3D

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Catalog Pages/Data Sheets

1773464-1_QRG_PIDG_TERMINALS_AND_SPLICES

PDF

English

Instruction Sheets

Instruction Sheet (U.S.)

Assembly Instructions For Knife Disconnects

PDF

English

Agency Approvals

UL Report

MODULAR PLUGS AND JACKS REPORT

PDF

English

WIRE CONN, TERMINALS, BUTT AND PARALLEL CONNECTORS-PLASTI-GRIP, SOLISTRAND, STD B, DIAMOND GRIP, PIDG AND AMPower REPORT

PDF

English

CSA Certificate

PLASTI-GRIP INSULATED BUTT SPLICES, TERMINAL SPLICES AND TERMINALS REPORT

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Insulated Yes

Insulated Wire Support Yes

Support Style Insulation Support

Body Features

Plating Material Copper, Tin

Insulation Sleeve Material Nylon

Dimensions

Wire Size (AWG) 22 – 16

Wire Size (mm²) .3 – 1.42

Wire Insulation Diameter (Max) 3.56 mm [.14 in]

Wire Size (CMA) 509 – 3260

Packaging Features

Packaging Method Box

Packaging Quantity 1000

Other

Barrel Color Red

PRODUCT COMPLIANCE



Statement of Compliance

[**Statement of Compliance**](#)

PDF
