2393866-1 ✔ ACTIVE



LUMAWISE | ALR AA

TE Internal #: 2393866-1

Electronic, 105 – 305 VAC, Commercial, 1800 VA Load Rating (Ballast), Fixed Mount, ALR AA, ANSI Street Lighting Photocells

View on TE.com >

Connectors > Lighting Connectors > Street Lighting Controls > Street Lighting Photocells




Product Availability: **Americas**

Street Lighting Photo Control Technology: **Electronic**

Operating Voltage Range: **105 – 305 VAC**

Grade: **Commercial**

Load Rating (Ballast): **1800 VA**

Features

Product Type Features

Street Lighting Photo Control Technology	Electronic

Configuration Features

Number of Positions	3

Electrical Characteristics

Operating Voltage Range	105 – 305 VAC
Load Rating (Ballast)	1800 VA
Load Rating (Tungsten)	1000 W
Fail Mode	On
Surge Protection	445 Joule
Relay Rating	30A General Purpose

Body Features

Lead Length	193.04 mm[7.6 in]
Primary Product Color	Black

Mechanical Attachment

Downloaded from Arrow.com.

Mounting Options	Fixed Mount

Dimensions

MOV Diameter	20 mm
Wire Size	16 AWG
Product Length	58.5 mm[2.3 in]
Product Width	33 mm[1.29 in]

Usage Conditions

Operating Temperature Range	-40 – 70 °C[-40 – 158 °F]

Operation/Application

Turn OFF Time Delay	2 – 5 seconds
Turn ON Light Level	1.5 fc
Turn ON Time Delay	Instant On seconds
Operating Frequency Range	50 – 60 Hz

Industry Standards

Compatible With Agency/Standards Products	UL
Compatible With Approved Standards Products	ANSI C136.24

Product Availability

Product Availability	Americas

Other

Grade	Commercial
OFF/ON Ratio	1.5:1

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per

Downloaded from Arrow.com.

	homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts




TE Part # 2324697-3
PUSH GRIP CONNECTOR 3P



TE Part # 2324697-2
PUSH GRIP CONNECTOR 2P



TE Part # 2324697-5
PUSH GRIP CONNECTOR 5P




TE Part # 2324697-6
PUSH GRIP CONNECTOR 6P



TE Part # 2324697-4
PUSH GRIP CONNECTOR 4P

Also in the Series | ALR AA



Street Lighting Photocells(9)

Customers Also Bought

Downloaded from Arrow.com.



TE Part #2213118-2
LUMAWISE LED HOLDER Z32 LOW PROFILE 1215



TE Part #CAT-526SDL-SEALTP
Sealed Connector: TPAs, Signal Double Lock, 2.5 mm



TE Part #2334614-4
Power Versa-Lock BACK COVER 4P



TE Part #2376865-4
Rcpt Assy, w/ intg gasket, PC, dimm 3 /4




TE Part #2377997-1
EP-II CONTACT LANCELESS, 18-16



TE Part #2382635-1
LUMAWISE POWER INPUT TERMINAL BLOCK (TB)



TE Part #2388553-5
PUSH-IN CONNECTOR, 5 POS



TE Part #2388950-1
ALR-8090-MFS-IP66



TE Part #2468181-1
LUMAWISE Endurance N+ 76mm, 7P, w/Vent

Documents

Product Drawings

ALR-AA-2000EL Photocontrol

English

CAD Files

Customer View Model

ENG_CVM_CVM_2393866-1_1.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_2393866-1_1.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2393866-1_1.3d_igs.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

Downloaded from Arrow.com.

LUMAWISE ALR AA Series

English

Product Specifications

Application Specification

English

Agency Approvals

UL

English

Downloaded from Arrow.com.