



Part Number : [1301020256](#)
Product Description : Safeway Phenolic Hand Lamp
Only with 100W, Screw Release Guard with Reflector,
with Side Outlet
Series Number : 130102
Status : Active
Product Category : Lamps and Lights
Engineering Number : 271U



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Lamps and Lights
Series	130102
Description	Safeway Phenolic Hand Lamp Only with 100W, Screw Release Guard with Reflector, with Side Outlet
NEMA Configuration	N/A
Product Name	Safety Yellow
Type	Hand Lamps
UPC	78678860132

Agency

CSA	LR85374
UL	E59251

Electrical

Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	240V

Physical

Bulb Type	Incandescent
Cord Length - Primary	N/A
Cord Length - Secondary	N/A
Depth	101.60mm (4.000")
Duty	Commercial
Guard Included	Yes
Guard Type	Reflector, Screw Release
Height	381.00mm (15.000")
Lamp Type	A21

Length	N/A
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Outlet	Side
Packaging Type	Carton

This document was generated on Sep 24, 2025