



Part Number : [350230014](#)

Product Description : 2.00mm Pitch, Board-In Crimp Housing, Right-Angle and Vertical, 14 Circuits, Natural

Series Number : 35023

Status : Active

Product Category : Connector Housings

---

## Documents & Resources

### Drawings

[Drawing 350230014\\_sd.pdf](#)

### 3D Models and Design Files

[3D Model 350230014\\_stp.zip](#)

### Specifications


[Packaging Specification PK-35023-001-001.pdf](#)

[Product Specification PS-35023-001-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

## Part Details

### General

Status	Active
Category	Connector Housings
Series	35023
Description	2.00mm Pitch, Board-In Crimp Housing, Right-Angle and Vertical, 14 Circuits, Natural
Application	Signal, Wire-to-Board
Product Family	Board-in Connectors
Product Name	Board-in
UPC	800753576575

### Agency

CSA	LR19980
UL	E29179

### Physical

Circuits (maximum)	14
Color - Resin	Natural
Flammability	94V-0
Gender	N/A
Glow-Wire Capable	No
Material - Resin	Nylon
Net Weight	0.273/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Stackable	No
Temperature Range - Operating	-40° to +105°C

## Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

## Use with Part(s)

Description	Part Number
2.00/2.50mm Board-in Terminal, Pre-Tin Plating, Wire Insulation Diameter 1.50mm max.	<a href="/content/molex/molex-dot-com/us/en/products/product-page.html/350449102.html">/content/molex/molex-dot-com/us/en/products/product-page.html/350449102.html</a>
2.00mm Pitch, Board-in Male Crimp Terminal, Right-Angle, Brass Tin (Sn) Plating, 24-30 AWG, Reel	<a href="/content/molex/molex-dot-com/us/en/products/product-page.html/350211201.html">/content/molex/molex-dot-com/us/en/products/product-page.html/350211201.html</a>
2.00mm Pitch, Board-in Male Crimp Terminal, Right-Angle, Pre-Plated, 24-30 AWG, Reel	<a href="/content/molex/molex-dot-com/us/en/products/product-page.html/350211301.html">/content/molex/molex-dot-com/us/en/products/product-page.html/350211301.html</a>
2.00mm Pitch, Board-in Male Crimp Terminal, Right-Angle, Post-Tin Plated, 24-30 AWG, Reel	<a href="/content/molex/molex-dot-com/us/en/products/product-page.html/350211360.html">/content/molex/molex-dot-com/us/en/products/product-page.html/350211360.html</a>

---

This document was generated on Jul 29, 2024